


| Item | Description |
|--|--|
| <p>Drive</p> <p>Application: All SRViper models</p> | <ul style="list-style-type: none"> • New Driven Shaft Assembly ✓ New increased cross-sectional area added to receive a new full-floating bearing. ✓ New nitride surface treatment: better resists fatigue and wear. ✓ Simple design, easy to replace.  <p>The diagram shows two driven shafts. The top shaft is labeled '30 mm' and '2016'. It has a larger diameter and a section labeled 'Full nitride surface treatment'. The bottom shaft is labeled '25 mm' and '2015'. It has a smaller diameter. Arrows indicate the increased diameter of the 2016 shaft compared to the 2015 shaft.</p> |

| Item | Description |
|--|--|
| <p>Drive</p> <p>Application: All SRViper models</p> | <ul style="list-style-type: none"> • New Reverse-Actuator Fasteners ✓ Actuator fasteners now include a washer. ✓ Washers provide a larger surface area to help reduce likelihood of actuator boss cracking from over-tightening. ✓ New part# 8JP-RA247-10 can be used on SRViper models (from 2014 and up). |

